



## Glass Wash

### Non DG Glass Washing Detergent

Excellent cleaning without streaking

Super concentrated for reduced costs

Quick break detergent for effective waste treatment of wash water

Biodegradable formulation

High Gloss Finish

#### Introduction

Glass Wash is a concentrated alkali based detergent for use in automatic glass washing machines. Glass Wash combines powerful detergents for removal of difficult residues such as lipstick, combined with anti-scaling agents and drying agents to leave glass surfaces clean and mark free.

#### Directions for use

Glass Wash should be used as supplied connected through glass washing machine dispensing systems. Dosing rates should be between 0.5% and 1.0% v/v for best results.

#### Safety

As this product is hazardous, it is recommended that gloves and safety glasses are worn when handling the concentrate.



Pack Size

3x5lt 15lt

Dilution Rate

0.5% - 1.0%